

Equipment Compatibility Guide

See data sheets for more detailed information, or contact your Clysar representative.

P=Preferred
A=Acceptable
NR=Not Recommended
S=Sprayed Version

WRAPPERTYPE/SEAL TECHNOLOGY							
	Anti-Fog AFG	High-Abuse ShrinkBox*	All-Purpose HP Gold*	"Wrap Anything" ABL	Low Shrink Force LE Gold	Thin LTC	PHOENIX™
L-Sealers							
Automatic L-Sealer	P	P	P	P	P	P	P
Semi-Automatic L-Sealer	P	P	P	P	P	P	P
Manual L-Sealer	P	P	P	P	P	P	P
Seal Technology							
Impulse Wire	P	P	P	P	P	P	P
Hot Knife	P	P	P	P	P	P	P
FFS-Cross							
Impulse Wire	A	P	P	P	P	P	P
Hot Knife	A	P	P	P	P	P	P
FFS-Side							
Single Wire	A	P	P	P	P	P	P
Dual Wire	A	P	P	P	P	P	P
Heated Ribbon	A	P	P	P	P	P	P
Heated Blade	A	P	P	P	P	P	P
Heated Wheels	A	P	P	P	P	P	P
Hot Air	A	P	P	P	P	P	P
FFS-Bottom (Lap Sealers)							
Thermal Seal	A	P	P	P	P	P	P
Static Seal	A	NR	A	A	A	A	A
Fin Trim	A	P	P	P	P	P	P
SPEED							
More than 80 FPM	NR	A	A	NR	NR	A	P
SLIP PROPERTIES							
Cold Slip	Med	Hi	Hi	Med	Med	Hi	Hi
Hot Slip	Low	NR	S	Low	S	S	Hi
PRE-TREATMENTS							
Print-Treated Available	Yes	No	Yes	No	No	Yes	No
Pre-Perforated Available	No	No	Yes	Yes	Yes	Yes	Yes

*Clysar® Bakery and Produce Films have the same equipment compatibility as HP Gold.