

Equipment Compatibility Guide

See data sheets for more detailed information, or contact your Clysar representative.

P=Preferred
A=Acceptable
NR=Not Recommended
S=Sprayed Version

WRAPPER TYPE/SEAL TECHNOLOGY	Anti-Fog AFG	High-Abuse ShrinkBox®	High-Speed EZ-R	High-Speed EZ Gold	All-Purpose HP Gold*	"Wrap Anything" ABL	Low Shrink Force LE Gold	Thin LTC	Thin LTCL	Thin LTCH
L-Sealers										
Automatic L-Sealer	P	P	A	A	P	P	P	P	P	A
Semi-Automatic L-Sealer	P	P	A	A	P	P	P	P	P	A
Manual L-Sealer	P	P	A	A	P	P	P	P	P	A
Seal Technology										
Impulse Wire	P	P	P	P	P	P	P	P	P	P
Hot Knife	P	P	A	A	P	P	P	P	P	A
FFS-Cross										
Impulse Wire	A	P	P	P	P	P	P	P	P	P
Hot Knife	A	P	A	A	P	P	P	P	P	A
FFS-Side										
Single Wire	A	P	P	P	P	P	P	P	P	P
Dual Wire	A	P	P	P	P	P	P	P	P	P
Heated Ribbon	A	P	A	A	P	P	P	P	P	A
Heated Blade	A	P	P	P	P	P	P	P	P	P
Heated Wheels	A	P	P	P	P	P	P	P	P	P
Hot Air	A	P	P	P	P	P	P	P	P	P
FFS-Bottom (Lap Sealers)	A	P	P	P	P	P	P	P	P	P
Thermal Seal	A	NR	A	P	A	A	A	A	A	P
Static Seal	A	P	P	P	P	P	P	P	P	P
Fin Trim										
SPEED										
More than 80 FPM	NR	A	P	P	A	NR	NR	A	NR	P
SLIP PROPERTIES										
Cold Slip	Med	Hi	Med	Med	Hi	Med	Med	Hi	Med	Med
Hot Slip	Low	NR	Hi	Hi	S	Low	S	S	S	Hi
PRE-TREATMENTS										
Print-Treated Available	Yes	No	Yes	Yes	Yes	No	No	Yes	No	Yes
Pre-Perforated Available	No	No	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes

*Clysar® Bakery and Produce Films have the same equipment compatibility as HP Gold.