

## Description

**Clysar® EVO-C™ Confidential** film is a tough, strong, opaque polyolefin shrink film made with Post-Consumer Recycled (PCR) content and prequalified for the **How2Recycle®** Store Drop-Off label. Ideal for confidential shipping and product containment, the versatile film offers UV protection and a high degree of puncture, tear and abrasion resistance.

A replacement for most non-recyclable shrink films or corrugate, Clysar® EVO-C™ Confidential film conforms to irregular shapes and seals reliably on a wide range of shrink equipment. The film offers a sustainable, cost-effective overwrap or secondary shipping material for applications requiring flexible sizing, security, privacy and product protection.



Prequalified for the  
**How2Recycle®**  
Store Drop-Off Label

Clysar, LLC  
888-4-CLYSAR  
marketing@clysar.com

Highway 67 South  
Clinton, IA 52732

[www.clysar.com](http://www.clysar.com)

# Clysar®

# Clysar® EVO-C™ Confidential Film DATA SHEET

## Uses

Clysar® EVO-C™ Confidential film is a market-leading sustainable security and shipping film. It is made with post-consumer recycled content and is prequalified for recycling in the Store Drop-Off stream by **How2Recycle®**.

The right-gauged opaque film delivers 90% opacity, UV-blocking properties and effective concealment, while using 30% less packaging material.

Applications include high-value products such as jewelry or electronics; sensitive printed or personalized materials; pharmaceuticals and supplements; official documents and forms; books, catalogs and magazines; footwear; sporting goods; and liquid or granular cleaning, personal care and household products.



Use to conceal and protect products shipped in an overbox or replace the outer shipping box completely.

## Significant Features

### Sustainability

- Made with Post-Consumer Recycled (PCR) content certified by SCS Global Services.
- Prequalified for Store Drop-Off by **How2Recycle®**.
- Provides 30% right-gauged solution over 150-gauge concealment films.
- Delivers significant material reduction, lowers DIM weight in comparison to corrugate.
- Requires less energy/lower temperature settings on sealers and shrink tunnels.



A sustainable and cost-saving alternative to bulky corrugate boxes.

### Sealing

- Provides strong, durable seals with most sealing systems.
- Wide sealing temperature range.
- Requires little or no cooling dwell.

### Shrinking

- Excellent cleanup for tight, attractive packages.
- High shrink force conforms to irregular shapes, offers excellent bundling capability.
- Excellent resistance to burn-through.

### General

- Delivers 90% opacity, blocking nearly 100% of UV light.
- Easy to run on most types of shrink equipment.
- Ultra-strong, puncture-, abrasion- and tear-resistant.
- May be printed or used with labels.

## Disposal

Preferred options for disposal are:  
(1) Store drop-off recycling; and (2)  
incineration with energy recovery.

## Storage

Storage below 32°C (90°F)  
is recommended. Prolonged  
exposure to temperatures  
moderately above 32°C (90°F) or  
brief exposure to temperatures  
well above 32°C (90°F) may cause  
difficulty in unwinding film.

For more detailed information on  
the safe handling of Clysar® films,  
a "Safety in Handling and Use"  
guide can be obtained from your  
Clysar representative.

## Standard Put-Ups

- 100 Gauge (90% Opacity for Privacy)
- Flat film is available in custom widths ranging from 3" up to 80" in ¼" increments.\*
- Folded film is available in custom widths from 3" up to 37" in ½" increments.\*
- Folded film will have half the linear footage of flat film for same gauge and roll dimensions.

\*Contact your Clysar representative for details.

## Shipping

Clysar® EVO-C™ Confidential film can be packaged in corrugate-free packaging (singles, efficiency or cradle pack) to support sustainability throughout the supply chain.

## Summary of Properties

### Clysar® EVO-C™ Confidential - Linear Footage Flat Film (Table 1)

Core I.D., in.	Roll O.D., in.	100 Gauge
3	10 1/2	5,250
3	14 1/2	10,500
6	12 1/2	5,250
6	15	10,500

### Typical Properties of Clysar® EVO-C™ Confidential (Table 2)

Property	ASTM Test Method	Unit	100 Gauge
Haze	D1003	%	NA
Gloss at 20°	D2457	(photocell)	75
Transmittance	D1003-13	%	10
COF, Kinetic	D1894	-	0.20
Shrink Force	D2838	g/in@100°C	105
Stiffness Modulus (avg)	D882	kpsi	85
Tensile Strength (avg)	D882	kpsi	14.9
Elongation (avg)	D882	%	118
Tear Strength (avg) (Elmendorf)	D1922	g	18
Spencer Impact	D3420	lbf	4

Note: These values are typical data for EVO-C™ Confidential shrink film and are not intended for use as limiting specifications.

## UV Status

Verified to block nearly 100% of UV light through independent lab testing.

## Recyclability

Clysar® EVO-C™ Confidential shrink film is approved for the Store Drop-Off label by **How2Recycle®**, and has obtained an official letter of prequalification.



Made with Post-Consumer Recycled (PCR) content certified by SCS Global Services.

Clysar, LLC  
888-4-CLYSAR  
marketing@clysar.com  
Highway 67 South  
Clinton, IA 52732  
[www.clysar.com](http://www.clysar.com)

# Clysar®

The technical data contained herein are guides to the use of Clysar® films. The advice contained herein is based upon tests and information believed to be reliable, but users should not rely upon it absolutely for specific applications because performance properties will vary with processing conditions. It is given and accepted at user's risk, and confirmation of its validity and suitability in particular cases should be obtained independently. Clysar makes no guarantees of results and assumes no obligations or liability in connection with its advice. This publication is not to be taken as a license to operate under, or recommendation to infringe, any patents. CAUTION: Do not use in medical applications involving permanent implantation in the human body. For other medical applications, see Clysar Medical Caution Statement, MCS\_02.